

## **FWSG 225**

### Scraper tool for pipes d 75 - d 225 (3" - 8" IPS)

Cross-dimension scraper tool FWSG 225

- Safe removal of the oxide layer from HD-PE and PE-Xa pipes
- Scraper blade made of hard metal with 2 cutting edges (double life)
- Universal scraping areas from d 75 d 225 (3" 8" IPS)
- Uniform chip removal by spring-mounted scraper blade and automatic feed
- With quick adjustment for easy adjustment to the scraping length
- Delivery in transport box



Reference	Article description	Diameter Area	вх	Weight kg
613409	FWSG 225	d 75 - d 225	1	4,835



# FRIATE

### **FWSG 225**

## Scraper tool for pipes d 75 - d 225 (3" - 8" IPS)

#### **Application**

FRIATOOLS scraper tools for the perfect preparation of HDPE pipe surfaces: Consistently uniform removal of oxide layers for the perfect electrofusion.

#### The crucial difference

Having the correct tools to perform installation on site makes all the difference. We see ourselves as spe cialists in the elec-trofusion of HDPE piping systems, so our development work has also included equipment and accessories for your needs from the very outset.

We know exactly what matters and what is needed in the field, and we can offer you a range of equip-ment tailored to the daily challenges en countered on the building site:

FRIATOOLS scraper tools for all pipe diameters and for a wide range of scrape lengths and saddle surfaces. These safeguard a uniform removal of material and repro-ducible quality for the optimal processing and reliable fusion of HDPE pipes.

Put your trust in tools that produce the perfect results.

#### Good reasons for the FRIATOOLS scraper tool FWSG225:

- Reliable removal of oxide layers on PE 80, PE 100, and PE-X pipes
- · NEW: With quick adjustment of the scraping length
- NEW: Replacement blade with 2 cutting edges for twice the service life
- Automatic compensation of pipe ovalities and tolerances
- Consistent swarf removal due to spring mounted scraper blade and automatic feed
- Easy handling with little effort
- · Maintenance-friendly due to use of wear-resistant materials
- · The tool is delivered in a transport box

